

ABOP 13-2 cordless drill

lithium-ion 18 V, in case



Application:

ideal for drilling in steel and stainless steel

Execution:

- metal gear head
- self-tightening drill chuck clamping jaws
- mechanical two-speed gear unit for optimum speed adaptation

Advantage:

- highest quality with high concentricity for precise drilling results

Delivery:

does not include battery or charger, includes additional handle, metal quick-action drill chuck, plastic case



Art. no.	71028 581
Model	ABOP 13-2 Select
Motor design	Brushless motor
Battery included	No
Number of rechargeable batteries/batteries	0
Battery voltage	18 V/AC
Max. drilling diameter in wood	37 mm
Max. drilling diameter in steel	13 mm
Idle speed 1st gear min./max.	0-580 rpm
Idle speed 2nd gear min./max.	0-1760 rpm
Max. torque hard/soft	24 / 8 Nm
Min./max. drill chuck span width	1.5-13 mm
Weight	2.4 kg
With working lights	No
With rubber-coated handle	Yes
With right/left-hand rotation	Yes
Product Group	Prod. Gr. 704

EAN

4014586881768