



GE
Lighting

20857 - GE ConstantColor® Precise™ MR16

Q20MR16C/CG40BAB

☞ UV protection

Product Photo



GENERAL CHARACTERISTICS

Base Description	2-Pin
Base Type	Pin/Plug-In
Filament	C-6
Rated Life Hours-nominal	5000 h
Lamp Enclosure Type	Covered glass
Product Technology	Halogen
Base	GU5.3
Bulb Shape	MR16

PHOTOMETRIC CHARACTERISTICS

Beam Spread	40 deg
Center Beam Candle Pwr Candela	475 cd
Initial Lumens-nominal	225 lm
Color Temperature	2900 K

PRODUCT INFORMATION

Product Code	20857
Description	Q20MR16C/CG40BAB
Alternative Unit Of Measure	BUNDLE
Standard Package Quantity	20
Ean UPC	043168992954
Standard Package GTIN	00043168208574
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	20
Sales Unit	Unit
UCC	043168208574

DIMENSIONS

Diameter	2 in
----------	------

ELECTRICAL CHARACTERISTICS

Burn Position	Universal burning position
Input Voltage [nom]	12 V
Rated power (Watts)	20 W

CAUTIONS & WARNINGS

Caution

- Lamp may shatter and cause injury if broken
- Do not use lamp if outer glass is scratched or broken.

Warning

Risk of Burn

- Allow lamp/fixture to cool before handling.

Pressurized lamp--unexpected rupture may cause injury, fire, or property damage

- Do not use lamp if outer glass is scratched or broken.

Risk of Fire

- Keep combustible materials away from lamp.
- Use in fixture rated for this product.