


Rohrschalter


Cylindrical Proximity Switches

Interrupteurs cylindriques

120 ...



122 ...



Typen Nr. type no. référence	Schaltspannung switching voltage tension de commutation	Schaltstrom switching current courant de commutation	Schaltleistung switching power pouvoir de coupure	Material material matériau
120 310	max. 250 V	max. 1,0 A	max. 20/30 W/VA	PA
120 320	max. 250 V	max. 1,0 A	max. 20/30 W/VA	PA
120 230	max. 48 V	max. 0,3 A	max. 3/3 W/VA	PA
122 310	max. 250 V	max. 1,0 A	max. 20/30 W/VA	PA
122 320	max. 250 V	max. 1,0 A	max. 20/30 W/VA	PA
122 230	max. 48 V	max. 0,3 A	max. 3/3 W/VA	PA

Typen Nr. type no. référence	Schutzart protection class protection	Temperaturbereich temperature range plage de température	Kontaktform* contact form* type de contact*	Kabel cable câbles
120 310	IP 67	-25...+75°C	A	PVC, 1 m ± 30 mm, 0,5 mm ²
120 320	IP 67	-25...+75°C	B	PVC, 1 m ± 30 mm, 0,5 mm ²
120 230	IP 67	-25...+75°C	C	PVC, 1 m ± 30 mm, 0,75 mm ²
122 310	IP 67	-25...+75°C	A	PVC, 1 m ± 30 mm, 0,5 mm ²
122 320	IP 67	-25...+75°C	B	PVC, 1 m ± 30 mm, 0,5 mm ²
122 230	IP 67	-25...+75°C	C	PVC, 1 m ± 30 mm, 0,5 mm ²