

PX0101P04GY Datasheet

Product Name // 4 Contacts Female Standard Rectangular Grey Connector

[View Product Page](#)



// Product Description:

- ⊗ 4 Contacts Female Standard Rectangular Grey Connector
- ⊗ Enhanced Seal Protection (ESR), Protective End Cap (PEC), Terminating Resistor (TER), Shrink Boot Adapter (SBA), Welded Flange (WFL) and Y-Type Connector (YTY) Available
- ⊗ Water and dustproof to IP68 when mated with compatible connector
- ⊗ Mate with PX0100 Series, as appropriate
- ⊗ Wedgelocks Available
- ⊗ Crimp Terminals
- ⊗ Mechanical Cycles=100 (min)
- ⊗ Operating Temperature= -25°C to +120°C

// General Information:

Product Configurator:	No
Product Display Title:	Standard Rectangular Connector Female
Product Family:	Rectangular Connectors
Product Series:	Standard Rectangular Connectors
Pdffbuilder Enabled:	Yes
Weight:	1
Body Colour:	Grey
Ip Rating:	IP68
Max Operating Temperature:	+120°C
Min Operating Temperature:	-25°C
Number Of Contacts:	4 Contacts
Product Technical Image:	/p/x/px0101_diagram.jpg
Package Id:	564

// Electrical Specifications:

Contact Type:	Plug Contact
Current Max:	13A
Voltage Max:	250V

// Mechanical Specifications:

Max Contact Accomodation Awg:	20AWG
Min Contact Accomodation Awg:	14AWG

// Material Information:

Body Material:	Polycarbonate/Polybutylene Terephthalate (PC/PBT)
----------------	---

// Product PDF Links

[Rectangular Power Connector...](#)

// Product 3D CAD Model Links

[PX0101P04GY3D CAD Model](#)