


TRMS DIGITAL MULTIMETER 40000 COUNTS

DMM9000BT



- LCD Display (40000 counts)
- High accuracy (0,03% on V DC)
- Bargraph
- LoZ mode
- High Frequency Rejection
- MAX/MIN/AVG
- Datalogging (40000 registers)
- REL
- AC/DC Voltage up to 1000 V
- AC+DC measurements
- AC/DC current up to 10A



DMM9000BT

TRMS DIGITAL MULTIMETER 40000 COUNTS

| General | |
|-------------------------------|--|
| Display | 40000 counts |
| Auto power off | ✓ |
| Backlight | ✓ |
| Bargraph | ✓ |
| REL | ✓ |
| HOLD | ✓ |
| High Frequency Rejection mode | ✓ |
| Diode and continuity test | ✓ |
| Auto-ranging | ✓ |
| MIX/MAX | ✓ |
| ZERO | ✓ |
| Non Contact Voltage Detection | ✓ |
| LoZ mode | ✓ |
| Wireless Conectivity | ✓ |
| Datalogging | 40000 |
| Dimensions | 83x188x52mm |
| Torch | ✓ |
| Weight | 465g |
| Batteries | NEDA 15A/IEC LR6, 2*1,5V |
| Standars | EC 61010-1, IEC/EN61010-2-033 |
| Safety rating | CAT IV 600V, CAT III 1000V |
| Accesories included | Standard test leads, thermocouple, hanging magnetic strap, PC communication cable, user manual |

DMM9000BT

TRMS DIGITAL MULTIMETER 40000 COUNTS

| Specs | |
|-------------------|-----------------|
| TRMS | ✓ |
| DC Voltage (mV) | 600mV |
| DC Voltage (V) | 1000V |
| AC Voltage (V) | 1000V |
| AC+DC Voltage (V) | ✓ |
| DC Current | 10A |
| AC Current | 10A |
| AC+DC Current (A) | ✓ |
| Frequency | 100kHz |
| Resistance | 40MΩ |
| Diode | 2V |
| Temperature | -200°C - 1200°C |

| Product Code Information | |
|--------------------------|-------------------|
| SKU | KPSDMM9000BTCBINT |
| EAN code | 8435394784731 |
| UPC code | 810053676646 |
| Pcs/export carton | 15 |