




C-HVPT2XXX

REV	ECN	DESCRIPTION	DATE	MODIFIED
2		PRE-RELEASE	Apr-08-16	JC

CUSTOMER DRAWING



C-HVPT2XXX

C-HVPT2XXX

HVPT 2 A XX




- 25: FOR 25mm² Shielded WIRE; OD = 11.9 ± 0.4mm
- 35: FOR 35mm² Shielded WIRE; OD = 14.2 ± 0.4mm
- 50: FOR 50mm² Shielded WIRE; OD = 16.5 ± 0.4mm
- 70: FOR 70mm² Shielded WIRE; OD = 19.0 ± 0.4mm

TECHNICAL DATA

OPERATING TEMPERATURE	-40 ~ 125 °C
SHIELDING	YES
WATERPROOF(MATED CONDITION)	IP67
AMBIENT TEMPERATURE	-40 ~ 70 °C

DIMENSIONS	TOLERANCES	PROJECTION	TITLE		
ANSI Y14.5M UNITS: MM Pro/E FILE	X ±0.5 .XX ±0.25 ANGLES ±0.5°		Amphenol Pcd Shenzhen HVPT 2X PASS-THRU CABLE SEAL GLAND		
ORIGINAL NOT FOR CUSTOMER DISTRIBUTION	<i>THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD SHENZHEN</i>	 JC Apr-08-16 CHKD APPD			

C-HVPT2XXX



SECTION A-A

PANNEL DRAWING

C-HVPT2XXX

C-HVPT2XXX

SIZE	DWG NO.	REV
A3	C-HVPT2XXX	2
CODE: 58982	SCALE: 1:1	SHEET 2 OF 2