

Interchangeable Plug in Power Supply

Features:

- Interchangeable AC Heads
- Compatible with Pi4
- Level VI Efficiency
- Worldwide Approvals



Specification:

Input Voltage Range	90-264 Vac
Input Frequency Range	47-63Hz
Input Current Rated	0.6A Max
Input AC Heads	UK, Euro, USA & Aus
Output Voltage Rating	+5.1V
Output Current Max	3A
Output Current Min	0A
Output Connection Type	Plug Type C
Total Output Regulation	+/- 5%
Line Regulation	+/- 2%
Ripple & Noise	240mVp-p
Efficiency	81.97% Min
Over Voltage Protection	10VDC maximum
Over Current Protection	5 A maximum with auto-recovery function
Short-Circuit Protection	The adapter shall not be damaged by short the DC output to Ground
Operating Temperature	0°C to +40°C
Storage Temperature	-20°C to +60°C
Operating Humidity	20 to 85%
Storage Humidity	5 to 95%
Hi-Pot	3000VAC 10mA 1min
Leakage Current	0.25mA max
Safety Standard	UL/CUL(UL62368), TUV-GS(EN62368), SAA(AS/NZS62368)
EMI Standard	FCC(PART 15 CLASS B), CE(EN55032), RCM
MTBF	50K Hours
Size mm max.	74.5 (L) x 36 (W) x 54(H)
Weight	115g ±15%

Art. Nr.

RND 320T7715DV

PRODUCT DRAWING:

