



PLUG-IN RELAY, COMPLETE UNIT 24 V DC, 3 CO CONTACT LED MODULE RED STANDARD PLUG-IN SOCKET SCREW TERMINAL 3.5 MM PINNING

Figure similar

General technical data:

Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> • for DC Rated value — minimum — maximum 	V	24
	V	24
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		3
Operating current of the auxiliary contacts		
<ul style="list-style-type: none"> • at DC-13 — at 24 V • at AC-15 — at 230 V 	A	8
	A	5
Design of the switching function positively driven		No
Switching behavior		monostable

Mechanical data:

Type of electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component Plug-in socket		Yes
Width	mm	28
Height	mm	72
Depth	mm	74

Certificates/ approvals:



[Declaration of Conformity](#)

Further information

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=LZS:PT3A5L24>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/LZS:PT3A5L24>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=LZS:PT3A5L24&lang=en

last modified:

15.01.2015