



### Main

Range of product	Lineryg
Product or component type	Cable end
Cable end size	Medium
Standards	NF C 63-023
Type of packing	String of bags
Quantity per set	10 sets of 100
Cable cross section	0.00 in <sup>2</sup> (0.75 mm <sup>2</sup> )

### Complementary

Cable end type	Single conductor
Additional information	Without marker tag holder
Color	Blue
Bezel material	Halogen-free plastic
Tube material	Copper ISO 1337
Number of cables	1
AWG gauge	AWG 20
Bezel size	Ø 3.3 mm
Tube diameter	0.06 in (1.5 mm)
Length	0.55 in (14 mm)
Tube length	0.31 in (8 mm)
Net Weight	0.22 lb(US) (0.1 kg)

### Environment

Product certifications	UL
Ambient air temperature for operation	-4...221 °F (-20...105 °C)

### Ordering and shipping details

Category	22621 - IEC PANEL ACCESSORIES
Discont Schedule	I
GTIN	00785901223092
Nbr. of units in pkg.	1000
Package weight(Lbs)	1000 lb(US) (453.59 kg)
Returnability	Yes
Country of origin	DE

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.16 in (0.4 cm)
Package 1 width	0.16 in (0.4 cm)
Package 1 Length	0.59 in (1.5 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	80000
Package 2 Weight	38.12 lb(US) (17.293 kg)

Package 2 Height	30.31 in (77 cm)
Package 2 width	31.50 in (80 cm)
Package 2 Length	23.62 in (60 cm)
Unit Type of Package 3	S03
Number of Units in Package 3	80000
Package 3 Weight	18.34 lb(US) (8.32 kg)
Package 3 Height	11.81 in (30 cm)
Package 3 width	11.81 in (30 cm)
Package 3 Length	15.75 in (40 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Halogen content performance	Halogen free product

### Contractual warranty

Warranty	18 months
----------	-----------