

Carbonfilm Resistors

CCR-02

(2 Flap FL24/10) 48 Values / 1.110 Pieces

Type/Fab: CFR25 (old 105-0) / Yageo Europe

Size: 0207 (2,3Øx6,3mm)

Value Range: 10Ohm-1Mohm (E6/E12)

Wattage: 0,25W

Tolerance: ±5%

Values-Quantities Selection:

10	30x	15	15x	22	15x	33	15x	47	15x	68	15x
100	30x	150	30x	180	15x	220	30x	270	15x	330	30x
390	15x	470	30x	560	15x	680	30x	820	15x	1K0	30x
1K2	15x	1K5	30x	1K8	15x	2K2	30x	2K7	15x	3K3	30x
3K9	15x	4K7	30x	5K6	15x	6K8	30x	8K2	15x	10K	30x
12K	15x	15K	30x	18K	15x	22K	30x	27K	15x	33K	30x
39K	15x	47K	30x	56K	15x	68K	30x	82K	15x	100K	30x

CCR-04

(5 Flap FL24/10) 120 Values / 2.340 Pieces
Binder: CCO-70 (Dimension: 318x260x70)

Type/Fab: 1 CFR25 (old 105-0) / Yageo Europe

Size: 0207 (2,3Øx6,3mm)

Value Range: 10Ohm-1M0hm (E24)

Wattage: 0,25W

Tolerance: ±5%

Values-Quantities Selection:

10	25x	11	5x	12	10x	13	5x	15	25x	16	5x
18	10x	20	5x	22	25x	24	5x	27	10x	30	5x
33	25x	36	5x	39	10x	43	5x	47	25x	51	5x
56	10x	62	5x	68	25x	75	5x	82	10x	91	5x
100	40x	110	10x	120	25x	130	10x	150	40x	160	10x
180	25x	200	10x	220	40x	240	10x	270	25x	300	10x
330	40x	360	10x	390	25x	430	10x	470	40x	510	10x
560	25x	620	10x	680	40x	750	10x	820	25x	910	10x
1K0	40x	1K1	10x	1K2	25x	1K3	10x	1K5	40x	1K6	10x
1K8	25x	2K0	10x	2K2	40x	2K4	10x	2K7	25x	3K0	10x
3K3	40x	3K6	10x	3K9	25x	4K3	10x	4K7	40x	5K1	10x
5K6	25x	6K2	10x	6K8	40x	7K5	10x	8K2	25x	9K1	10x
10K	40x	11K	10x	12K	25x	13K	10x	15K	40x	16K	10x
18K	25x	20K	10x	22K	40x	24K	10x	27K	25x	30K	10x
33K	40x	36K	10x	39K	25x	43K	10x	47K	40x	51K	10x
56K	25x	62K	10x	68K	40x	75K	10x	82K	25x	91K	10x
100K	40x	110K	10x	120K	25x	130K	10x	150K	40x	160K	10x
180K	25x	200K	10x	220K	40x	240K	10x	270K	25x	300K	10x
330K	40x	360K	10x	390K	25x	430K	10x	470K	40x	510K	10x
560K	25x	620K	10x	680K	40x	750K	10x	820K	25x	1M0	40x

CCR-06**(1 Flap FL24/10) 24 Values / 288 Pieces****Type/Fab:** NAS1/2 / Hokuriku or alternative**Size:** 0411 (3,7Øx8,5mm)**Value Range:** 0,47Ohm-8,2Ohm (E12) 1,2MOhm-4,7MOhm (E12)**Wattage:** 0,5W**Tolerance:** ±5%**Values-Quantities Selection:**

R47	30x	R56	15x	R68	30x	R82	15x	1R0	30x	1R2	15x
1R5	30x	1R8	15x	2R2	30x	2R7	15x	3R3	30x	3R9	15x
4R7	30x	5R6	15x	6R8	30x	8R2	15x	1M2	15x	1M5	30x
1M8	15x	2M2	30x	2M7	15x	3M3	30x	3M9	15x	4M7	30x