


Category (ETIM):	Device mount IP 54
Type:	Device mount IP54-SDGSOT LED
Order number:	18620304100
Configuration:	Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Operating device:	Electronic driver (1 pcs.)
Mains voltage:	230V / 50Hz
System performance (W):	56
Luminaire luminous flux (lm):	8000
lm/W:	139
Ambient temperatures:	-20°C / 35°C
Certifications:	IP 54, protection class I, F, D, DIN10500/Food, Indoor, CE
Colour of the housing:	traffic white RAL 9016
Weight (net) (kg):	1.9
Dimensions LxWxDxH (mm):	1531 x 55 x 37
mounting method:	Mounting rail system mounting
EAN-number:	4020863325931
Commodity code:	94051098


SDGSOT LED 8000lm 840 • vw • ED • 18620304100



Lighting technology
Individual.Lens.Optic-direct narrow distribution
SDGSOT LED 8000 lm 840



η_{LB}	100 %
lm/W	139
$\Phi_{\downarrow/\uparrow}$	99 % / 1 %
UGR q/l	19.5 / 21.5



Quick-fit mounting system Device mount IP 54; Device mount made of galvanised, profiled sheet steel, surface coated with polyester resin enamel. Toolless fastening with two integrated pressure locks. Lighttechnical element with transparent seal, end faces made of plastic, all-round closed seal to mounting rail. Housing colour traffic white RAL 9016; Direct, open light distribution, individual. lens. optic made of polycarbonate. Heat-resistant cables including fixed 3-pole rapid installation plug connector with tool-less phase pre-selection and locating finger.

Dimensions LxWxDxH (mm): 1531 x 55 x 37
Configuration: Lamps integrated: LED, Light colour 840/neutral white (4000K), Colour rendering Ra>80; LED service life 50000h L80/B10
Luminaire luminous flux (lm): 8000
lm/W: 139
Operating device: Electronic driver (1 pcs.)
System performance (W): 56
Conditions: Suitable for use in ambient temperatures of -20°C to 35°C
Certifications: IP 54, protection class I, F, D, DIN10500/Food, Indoor, CE

Regiolux GmbH
Type: SDGSOT LED 8000 840 ET vw
Article number: 18620304100
Product deep link: <http://www.regiolux.de/de/article/18620304100>
5 year guarantee after registration on website.