

Clamping heads, round version

ORION®

Application:

Versatile in application, machining centres, all common axial force clamping systems on lathes and vices, measuring machines or pallet clamping.

Execution:

- High-strength rubber/metal connection
- High retention forces
- Corrosion protection coating

Art. no.	22001 394
Brand	ORION
Manufacturer Part Number	22001394
Size	80
Design	Without stem
Profile shape	Round and smooth
Clamping diameter	19 mm
Length	53 mm
Min./max. clamping range diameter	5-80 mm
Gross Weight	2.090 kg
Product Group	2AO



EAN

4053625469987