







REVISION RECORD

REV	ECN	DESCRIPTION	DRT	DATE



NOTES:

1. DIMENSION SHALL BE INTERPRETED PER ASME Y14.5-2009.
2. PITCH: 5.0MM, POLES: 02-24P
3. RATED VOLTAGE/CURRENT: UL 300V/15A VDE 320V/18A
4. OPERATION TEMPERATURES: -40°C~+105°C
5. RATED IMPULSE VOLTAGE: 4.0KV
6. WIRE RANGE: 28~12AWG, 1.0~2.5MM²
7. MAX. TORQUE VALUE: M3, 6.0kgf.cm
8. UNDIMENSIONED TOLERANCES:

PITCH RANGE	NOMINAL DIMENSION RANGE			
	IN	MM	IN	MM
TO OVER	TO OVER	TO OVER	TO OVER	TO OVER
6 TO 10	10 TO 24	30 TO 60	100 TO 150	OVER 150
±0.10	±0.15	±0.25	±0.30	±0.50
				±1.00
				±0.05/10

仅供参考图
签字: 葛利林
日期: 2018.8.20

ITEM	NAME OF PART	NO. OF PART	Q'TY	MATERIAL	NOTES
6	ZEDGK SCREW (M2.5)	S000001370(H)	2	Steel	Zn plated
5	ZEDGK-1000A SCREW (M3)	S000006350(H)	XX	Steel	Zn plated
4	ZEDGK-1000A CAGE	X000005080(H)	XX	Brass	Ni plated
3	ZEDGKA-1000A CLAMP	1028B00040(H)	XX	Phosphor bronze	Sn plated
2	ZEDGKA/B-5.0-1000A COVER	1030CYYYYX(H)	1	PA66	UL94V-0
1	ZEDGKA/BM-5.0-1000A HOUSING	1031AYXXE(H)	1	PA66	UL94V-0

DETACHED LISTS

TOLERANCES EXCEPT AS NOTED		FINISH:		MATERIAL:	
MM	(INCH)	XXX ±	.XX ±	XXX ±	.XX ±
THIRD ANGLE PROJECTION		APPR: <i>Rab in 2018.8.20</i>		NAME: DEGSON 宁波高正电子有限公司	
DRT: XXX 10/10/14"		CHKO: <i>[Signature]</i>		DEGSON® DEGSON ELECTRONICS CO., LTD	
		DRAWING NO.: ZEDGKBM-5.0-E05		TITLE: ASSEMBLY DRAWING	
		DO NOT SCALE DRAWING		SCALE 1:1	
				REV TO-1	
				SHEET 1/1	