


Product image / Drawings



X = wall thickness

X	Y	Z
0.75 ... 1.25	19.2 -0.1	12.9 +0.1
1.25 ... 2	19.4 -0.1	12.9 +0.1
2 ... 3	19.8 -0.1	12.9 +0.1

Technical data

Product number	1852.1102	
Business unit	Switches & Sensors	
Product Manager	Mattes	
Product family	Rocker switches	
Actuation type	direct	
Packing unit	300	
ROHS conform	yes	
Switching function	ON / OFF switch (DPST)	
Material fixed contact	Ag	
Number of poles	2-polig	
connections	Quick-connect terminal, 4.8 x 0.8	
Mechanical life endurance	5E4	
Rating IEC	4 (1) A 250 V AC	
Rating North America	4 A 250 V AC 1/10 HP 6 A 125 V AC 1/10 HP	
Temperatures	Connection side max.	85 °C
	Actuation side max.	55 °C
Actuators and additional actuators	rocker: PA, black, identification red on top visible in OFF position	
Housing description	housing: PA, black	
Connection surface	bearing connection	silver plated

	external connection	silver plated
Contact material	Ag	
Rating Code UL	R 52	
Contact type	lifting contact	
Approval marks	CSA / ENEC 05 / UL	
Suitable for appliances of protection class	II	
Additional labeling	year/week of manuf. acc. to DIN EN 60062	
Type of fastening	Snap fastening	
Stock version	●	