

The right label for virtually every situation and surface.



D1



D1



IND



Standard

D1 Standard Labels

For hundreds of tasks around the office or home office, such as filing, storage and asset management.

Available in continuous label cassettes, so you can create sharp, easy-to-read labels of just about any length.



Medium strength

D1 Permanent Labels

Look the same as standard labels but offer a powerful, permanent adhesive for when you want a label to stay put indefinitely.

D1 Flexible Labels

For curved and/or heavily textured surfaces and flag-marking cables. Permanent adhesive means labels will stay put.



Heavy duty

Indoor/Outdoor Vinyl

Ideal for both indoor and outdoor applications. Available in the widest range of colours that meet OSHA, ANSI and ISO colour standards.

Permanent Polyester

Professional polished finish ideal for panels, blocks, faceplates, shelves, bins, beams and more.

Flexible Nylon

Labels conform and stick tightly to wires, cables, curved and textured surfaces.

Heat-Shrink Tube

Print on 3:1 heat-shrink tubing for high-end cable ID and harness bundling.

D1 labels feature*:



Easy-Peel Backing
Quickly and easily remove label backing for trouble-free application



UV Resistant



Water Resistant



Cold/Heat Resistant

Industrial labels feature**:



Easy-Peel Backing



UV Resistant



Water Resistant



Cold/Heat Resistant



Oil Resistant



Chemical Resistant

* Details see page 26

** Details see page 27

D1 Label | Overview

DYMO® D1 Labels

Available in continuous label cassettes, so you can create sharp, easy-to-read labels of just about any length.



LABEL TYPE / TAPE WIDTH			24 mm	19 mm	12 mm	9 mm	6 mm
D1 STANDARD	For hundreds of tasks around the office or home office, such as filing, storage and asset management. Cold/Heat Resistance: -18°C to 90°C Length: 7 m	BLACK ON WHITE	S0720930	S0720830	S0720530	S0720680	S0720780
		BLACK ON CLEAR	S0720920	S0720820	S0720500	S0720670	S0720770
		BLACK ON YELLOW	S0720980	S0720880	S0720580	S0720730	S0720790
		BLACK ON BLUE	S0720960	S0720860	S0720560	S0720710	–
		BLACK ON GREEN	S0720990	S0720890	S0720590	S0720740	–
		BLACK ON RED	S0720970	S0720870	S0720570	S0720720	–
		WHITE ON CLEAR	S0721000	S0720900	S0720600	–	–
		WHITE ON BLACK	S0721010	S0720910	S0720610	–	–
		BLUE ON WHITE	S0720940	S0720840	S0720540	S0720690	–
		BLUE ON CLEAR	–	–	S0720510	–	–
		RED ON WHITE	S0720950	S0720850	S0720550	S0720700	–
		RED ON CLEAR	–	–	S0720520	–	–
D1 PERMANENT	Look the same as standard labels but offer a powerful, permanent adhesive for when you want a label to stay put indefinitely. Cold/Heat Resistance: -40°C to 150°C Length: 5.5 m	BLACK ON WHITE	–	S0718070	S0718060	–	–
D1 FLEXIBLE	For curved and/or heavily textured surfaces and flag-marking cables. Its permanent adhesive means it will stay put. Cold/Heat Resistance: -10°C to 80°C Length: 3.5 m	BLACK ON WHITE	–	S0718050	S0718040	–	–

For use with LabelManager™ series and LabelWriter™ 450 Duo

D1 labels feature:



Easy-Peel Backing
Quickly and easily remove label backing for trouble-free application



UV Resistant



Water Resistant



Cold/Heat Resistant