
Pluggable Terminal Blocks

Clamp Terminal 5.08 mm Pitch







| FEATURES: | | |
|----------------------------------|----------|--|
| Reversed | | |
| Polarised Mouldings | | |
| Withstand Voltage - AC2000V/1Min | | |
| Guided pin alignment | | |
| SPECIFICATION: | | |
| Pitch | 5.08 mm | |
| Gender housing | Female | |
| Connection direction | vertical | |

| Pitch | 5.08 mm | |
|--------------------------|----------------------------------|--|
| Gender housing | Female | |
| Connection direction | vertical | |
| Termination type | Clamp Terminals/Screw Connection | |
| Connection cross-section | 0.33-2 mm² (22-14AWG) | |
| Colour | green | |
| Rated voltage to EN | 250 V | |
| Rated current to EN | 15 A | |
| Rated voltage to UL | 250 V | |
| Rated current to UL | 15 A | |
| Temperature range | -33+120 °C | |

PRODUCT RANGE:

| Art. no. | Pole no. | |
|---------------|----------|--|
| RND 205-00375 | 2 | |
| RND 205-00376 | 3 | |
| RND 205-00377 | 4 | |
| RND 205-00378 | 5 | |
| RND 205-00379 | 6 | |
| RND 205-00381 | 8 | |
| RND 205-00382 | 9 | |