

## HYGST-3LPSK

Plug and socket with latch including covers



### SPECIFICATION

Number of Poles	3
Terminal Material	Plate brass/stainless steel spring
Body Material	Polyamide 66
Colour	Black
UL94 Rating	V2
Min Conductor Size (Sq mm)	0.5
Max Conductor Size (Sq mm)	2.5
Max Current (A)	16
Max Voltage (V)	250
Working Temperature	T110
Max Temperature Rating °C	110
Height (mm)	21
Width (mm)	28
Length (mm)	55
Comments	Product dimensions refer to individual products when component parts are assembled

### DISTRIBUTORS

