

Power Supply

AM1-2405SZ
Order Number: 70114140

Main Parameters (*)	min	typ	max	Unit
Operating Voltage	21.6	24	26.4	V DC
Operating Temperature	-40		85	°C
Storage Temperature	-40		125	°C

Technical Parameters

Lifetime	> 50,000 h
RoHS	yes

Mechanical Parameters

Size	11.68x6x9.65 mm
Weight	1.5 g


(*) Over the complete operating temperature range

Features



- Pin 1: -V Input
- Pin 2: +V Input
- Pin 3: -V Output
- Pin 4: +V Output

Picture



Safety Label



Valid Revision

1 | 21-MAY-2019