


Specifications

No. of Switch Positions	: 8 Position
No. of Poles	: 8 Pole
Angle of Throw	: 45°
Illumination	: Non Illuminated
Contact Current DC Max	: 25mA
Contact Voltage DC Max	: 24V


Materials:

Cover	: Nickel silver
Contact	: Alloy copper
Spring plate	: Stainless steel
Terminal	: Brass with silver plated

Diagram



Changeover Timing



Changeover Angle

	MODE1	MODE2	MODE3	MODE4	MODE5	MODE6	MODE7	MODE8
COM-A	ON	OFF	OFF	OFF	OFF	OFF	OFF	ON
COM-B	ON	OFF	OFF	OFF	OFF	OFF	OFF	ON
COM-C	ON	OFF	OFF	OFF	OFF	OFF	OFF	ON
COM-D	ON	OFF	OFF	OFF	OFF	OFF	OFF	ON

Part Number Table

Description	Part Number
Rotary Switch, 8 Position, 8 Pole, 45 Deg.	MCSR8-8R8G

Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.