

Product information

77 41 115

Electronics Diagonal Cutter

DIN ISO 9654



- For fine cutting work, e.g. in electronics and fine mechanics
- Load-optimised for a more direct feel when working
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 60 HRC
- Narrow sleeves pulled up to the head of the pliers enable the tool to be guided securely and comfortably, also between thumb and index finger
- Ball bearing chrome steel, oil hardened



General	
Article No.	77 41 115
EAN	4003773082316
Head	mirror polished
Handles	with multi-component grips
Weight	50 g
Dimensions	115 x 66 x 11 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 0.8 mm
Cutting capacities soft wire (diameter)	Ø 1.3 mm
Jaw length (B)	13 mm
Jaw thickness (joint) (D)	7 mm
Head width (A)	11 mm

technical change and errors excepted

