



A unique, patented alarm bell designed for use in fire, security and other signalling systems. The combination of a miniature solenoid with an integrated control circuit allows excellent sound coverage, minimum current consumption and increased reliability. The improved aesthetics make the bell suitable for all applications including the most prestigious locations.

- 152mm (6") GONG
- HIGH SOUND OUTPUT
- LOW CURRENT CONSUMPTION
- SIMPLE INSTALLATION
- NO BACKBOX REQUIRED FOR SURFACE WIRING
- WEATHERPROOF (WP) OPTION AVAILABLE

Specification

Voltage	12Vdc	24Vdc	230Vac
Current	12 Vdc	55 - 65mA	
	24 Vdc	25 - 35mA	
	230 Vac	20 - 30mA	
Sound Output	93 - 95dB(A)		
Monitoring	Reverse polarity (dc only)		
Temperature	- 25°C to + 70°C		
Protection	IP21C / IP33C (WP)		
Construction	Gong -Steel, Base - Polycarbonate		
Weight	12 Volt	1.1Kg	
	24 Volt	1.1Kg	
	230 Volt	1.2Kg	
Colours	Gong - Red	Base - Black	