

Counter scales IFS



Application:

Heavy industry standard suitable for harsh use

Execution:

- Ergonomic evaluation unit with large key block and high-contrast LCD displays for convenient input and reading, e.g. of tare values, reference weights, limit values etc.
- Three displays for weight display, reference weight, total number of pieces
- 100 item memory locations for master data such as reference weight, reference quantity, container weight (prior tare deduction) etc.
- Accurate counting: Manual reference optimisation gradually improves the average part weight
- Adding up counting parts
- Printing of date and time
- with comfortable numeric keypad for convenient data entry

Delivery:

with power supply unit and work protection hood



Art. no.	49000 087
Brand	KERN
Manufacturer Part Number	IFS 10K-4
Type description	IFS 10K-4
Max. weight measuring range	15000 g
Digit increment, weight	0.1 g
Digit height	16.5 mm
Plate size	240 x 300 mm
With unit counting	Yes
Min. item weight	2 g
Data transmission type	RS232
Linearity	0.4 g
Linearity 2	0.8 g
Reproducibility	0.1 g
Material of cover panel	Stainless steel
Display type	LCD
Gross Weight	7.060 kg
Product Group	447

EAN

4045761144866