

# MSR Gold™ MiniFastFit (Touring/Stage)

## MSR Gold™ 400 MiniFastFit 1CT



Thanks to the specially designed lamp base, the MSR Gold™ MiniFastFit takes just seconds to replace, to help ensure non-stop clubbing entertainment. In addition, the innovative gold plated pins ensure excellent current transfer to prolong lamp and lamp holder lifetimes and thereby reduce lamp replacement costs. Easy handling and small compact fixture designs are allowed by the lamps compact size, while the very short arc provides a high perceived brightness and high beam intensity.

## Product data

### • General Characteristics

System Description	MiniFastFit
Cap-Base	PGJX28
Cap-Base Information	PGJX28
Execution	-
Operating Position	any
Main Application	Entertainment
Life to 50% failures EM	750 hr

### • Light Technical Characteristics

Color Code	-
Color Rendering Index	60 Ra8
Color Temperature	6700 K
Color Temperature Technical	6700 K
Chromaticity Coordinate X	310 -
Chromaticity Coordinate Y	320 -
Luminous Flux Lamp EM	24000 (min), 26000 (nom) Lm
Luminous Efficacy Lamp EM	65 Lm/W

### • Electrical Characteristics

Lamp Wattage	400 W
Lamp Wattage Technical	400 W
Lamp Current	7.2 A
Ignition Supply Voltage	198 (min) V

Dimmable Yes

### • Luminaire Design Requirements

Pinch Temperature	500 (max) C
Bulb Temperature	950 (max) C

### • Product Dimensions

Overall Length C	111 (max) mm
Diameter D	23.2 (max) mm
Width F	35.3 (min), 36 (nom), 36.5 (max) mm
Light Center Length L	55 (min), 56 (nom), 57 (max) mm
Arc Length O	3.0 mm


### • Product Data

Order code	928194005114
Full product code	928194005114
Full product name	MSR Gold™ 400 MiniFastFit 1CT
Order product name	MSR Gold 400 MiniFastFit 1CT/16
Pieces per pack	1
Packing configuration	16
Packs per outerbox	16
Bar code on pack - EAN1	8718291158288
Bar code on outerbox - EAN3	8718291158295
Logistic code(s) - 12NC	928194005114
Net weight per piece	0.053 kg

# PHILIPS


# MSR Gold™ MiniFastFit (Touring/Stage)

## Dimensional drawing



### MSR Gold™ 400 MiniFastFit 1CT

Product	A (Min)	A (Norm)	A (Max)	C (Max)	D (Max)	D1 (Norm)	F (Min)	F (Norm)	F (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
MSR GOLD 400 MiniFastFit	-	-	-	111	23.2	-	35.3	36	36.5	55	56	57	3.0



© 2014 Koninklijke Philips N.V. (Royal Philips)  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2014, October 31  
data subject to change