



RIGHT ANGLE ADAPTER, 1:1, MALE, FEMALE, 9-PIN FOR SCREW CONNECTION TO RS485/422 INTERFACE OR RS 232 INTERFACE

Product type designation	
Installation type/mounting	
Wall mounting/direct mounting possible	Yes; Can be screwed onto the HMI
Interfaces	
Number of pins HMI-side	9; Male
Number of pins device-side	9; Female
Standards, approvals, certificates	
CE mark	Yes
Ambient conditions	
Ambient temperature in operation	
• Min.	0 °C
• max.	55 °C
Storage/transport temperature	
• Min.	-20 °C
• max.	70 °C
Relative humidity	
• Operation, max.	95 %
Mechanics/material	
Screw type	
• 4.5 V	Yes; HMI page
Type of housing (front)	
• Cast light alloy	Yes

Dimensions	
Width	31 mm
Height	25 mm
Thickness	25 mm

Weights	
Without packaging	34 g

Scope of supply	
Delivery unit in items	1

other	
Note:	suitable for all appropriate interfaces

Usable in the following products	
• Product 1	6AV6642-0*
• Product 2	6AV6542-0*
• Product 3	6AV6545-0*
• Product 4	6AV6644-*
• Product 5	6AV6545-8*
• Product 6	6AV6640-0C*
• Product 7	6AV6643-7BA00-*
• Product 8	6AV6643-7CD00-*
• Product 9	6AV6643-7DD00-*
• Product 10	6av2124-0*
• Product 11	6av2124-1*
• Product 12	6AV2124-2*
• Product 13	6AV6647-0*
• Product 14	6AV6643-8*
• Product 15	6AV2123-2*

last modified: 12.03.2015