






Number of contacts

8

50 V
5 A
+ shielding

Identification	Wire cross section (mm ²)	Part number male female		Drawing Dimensions in mm												
<p>Han-Modular®, Han® GigaBit Insert, Crimp terminal</p>  <p>Please order crimp contacts separately. Please order the adapter module separately.</p>		09 14 008 3011	09 14 008 3111	 <p>Cable outside diameter 5 ... 12</p>												
<p>Han-Modular®, Adapter module</p>  <p>Han® D-Sub crimp contact, turned contacts</p> 	<p>0.09 – 0.25 0.13 – 0.33 0.25 – 0.52</p>	<p>09 14 001 3011</p> <p>09 67 000 7576 09 67 000 5576 09 67 000 8576</p>	<p>09 14 001 3111</p> <p>09 67 000 7476 09 67 000 5476 09 67 000 8476</p>	 <table border="1" data-bbox="1037 1545 1500 1680"> <thead> <tr> <th>Wire gauge</th> <th>max. insulation diameter</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.09-0.25 mm²</td> <td>1.7</td> <td>4 mm</td> </tr> <tr> <td>0.13-0.33 mm²</td> <td>1.7</td> <td>4 mm</td> </tr> <tr> <td>0.25-0.52 mm²</td> <td>1.7</td> <td>4 mm</td> </tr> </tbody> </table>	Wire gauge	max. insulation diameter	Stripping length	0.09-0.25 mm ²	1.7	4 mm	0.13-0.33 mm ²	1.7	4 mm	0.25-0.52 mm ²	1.7	4 mm
Wire gauge	max. insulation diameter	Stripping length														
0.09-0.25 mm ²	1.7	4 mm														
0.13-0.33 mm ²	1.7	4 mm														
0.25-0.52 mm ²	1.7	4 mm														

Han-Modular