

EPIC® MH 8.0mm Contacts

High flexibility by the use of any combination of inserts in one connector

Info

Stamped gold plated contacts with 0.8mm diameter for D-Sub inserts



Voltage



Wind Energy



Rail



Mechanical and plant engineering



Automation & fältinstallation



Flame-retardant

Benefits

Crimp connection for permanent vibration proof contact
EPIC® MH system is mateable with the market standard

Application range

Mechanical engineering
Robot-building
Plant engineering
Renewable energy
Railway applications / vehicle construction

EPIC® MH 8.0mm Contacts

Technical Data

Classification:	ETIM 5.0 Class-ID: EC000796 ETIM 5.0 Class-Description: Contact for industrial connectors
Contact resistance:	< 5 mOhm
Termination methods:	Crimp termination: 10 mm ² ... 35 mm ²
Stripping length (mm):	18
Cycle of mechanical operation:	500

Note

Photographs are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.

**EPIC® MH 8.0mm Contacts**

Article number	Article description	Contact type	Connection cross section (mm ²)
EPIC® MH D=8.0 contacts			
44423242	EPIC® MH SCEM AG 10sqmm D=8.0	male	10
44423246	EPIC® MH BCEG AU 0.09 - 0.25sqmm D=1.0	female	10
44423243	EPIC® MH SCEM AG 16sqmm D=8.0	male	16
44423247	EPIC® MH BCEM AG 16sqmm D=8.0	female	16
44423244	EPIC® MH SCEM AG 25sqmm D=8.0	male	25
44423248	EPIC® MH BCEM AG 25sqmm D=8.0	female	25
44423245	EPIC® MH SCEM AG 35sqmm D=8.0	male	35
44423249	EPIC® MH BCEM AG 35sqmm D=8.0	female	35

Last Update (25.10.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.deYou can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16