



<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub>	d <sub>3</sub> ≈	h	t min.
20	M 5      M 6	12	30	18
25	M 6      M 8	15	38	18
30	M 8      M 10	18	46	18
35	M 10     M 12	21	53	21

**Ausführung**

- Kunststoff  
Duroplast (PF)  
- temperaturbeständig bis 110 °C  
- schwarz, glänzend
- *Kunststoff-Eigenschaften* → Seite 2158
- RoHS

Bestellbeispiel	
<sup>1</sup>	d <sub>1</sub>
<sup>2</sup>	d <sub>2</sub>
<b>GN 419-25-M8</b>	

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4

