

**SAK Series**  
**Q 10 SAK6N**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com


**Klippon® Connect with clamping yoke Technology**

The high reliability and variety of designs of the terminal blocks with clamping yoke connections make planning easier and optimises operational safety. Klippon® Connect provides a proven response to a range of different requirements.

**General ordering data**

Type	Q 10 SAK6N
Order No.	<a href="#">0457000000</a>
Version	SAK Series, Cross-connector, for cross-connection link, No. of poles: 10
GTIN (EAN)	4008190153762
Qty.	20 pc(s).

**SAK Series**  
**Q 10 SAK6N**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com

**Technical data****Dimensions and weights**

Width	77.1 mm	Width (inches)	3.035 inch
Height	6 mm	Height (inches)	0.236 inch
Depth	20.5 mm	Depth (inches)	0.807 inch
Net weight	24 g		

**Material data**

Material	CuSn	Colour	Grey
----------	------	--------	------

**System specifications**

Version	for cross-connection link	Tightening torque (cross-connector)	0.5...1 Nm
Mounting rail	none		

**Additional technical data**

Explosion-tested version	No	Installation advice	Direct mounting
Type of fixing	Screwed		

**Dimensions**

Pitch in mm (P)	8 mm
-----------------	------

**Rating data**

Rated current	41 A
---------------	------

**Classifications**

ETIM 3.0	EC000489	ETIM 4.0	EC000489
ETIM 5.0	EC000489	ETIM 6.0	EC000489
UNSPSC	30-21-18-01	eClass 5.1	27-14-11-40
eClass 6.2	27-14-11-40	eClass 7.1	27-14-11-40
eClass 8.1	27-14-11-40	eClass 9.0	27-14-11-40
eClass 9.1	27-14-11-40		

**Approvals**

ROHS	Conform
------	---------

**Downloads**

Engineering Data	<a href="#">EPLAN, WSCAD</a>
------------------	------------------------------