

Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

In the case of first time connection to speakers, headphones or other devices, the sound channel will take precedence. Audio preference can be changed via your System Preference Menu.

USB-C Dual Display Dock, 4K HDMI, VGA, 4K Mini DP, Gbe, Card Reader, 3x USB-A Ports, PD Charging, Silver

MODEL NUMBER: U442-DOCK1









Convert your MacBook, Chromebook, tablet or laptop into a versatile workstation via its USB-C or Thunderbolt 3 port. Recommended for connecting an external display, accessing Gigabit Ethernet, transferring data and displaying video.

Description

The U442-DOCK1 USB 3.1 Gen 1 USB-C Docking Station turns your MacBook, Chromebook, tablet or laptop into a versatile workstation. By connecting its built-in cable to your device's USB-C or Thunderbolt 3 port, you'll be able to add an external display, access Gigabit Ethernet networks, transfer data, display video and more.

Mini DisplayPort (mDP), VGA and HDMI ports allow you to connect an external display (one display at a time). With the addition of adapters (sold separately), you can also add a DVI or DisplayPort display to the U442-DOCK1. The mDP and HDMI ports support UHD video resolutions up to 3840 x 2160 (4K x 2K) at 30 Hz. The VGA port supports HD video resolutions up to 1920 x 1200, including 1080p, at 60 Hz.

Connect a Gigabit Ethernet cable (sold separately) to the RJ45 port to access true 10/100/1000 Mpbs network speeds. Three USB-A hub ports are convenient for connecting peripherals to your device. Each supports data transfer rates up to 5 Gbps. A dedicated BC 1.2-compliant USB port provides up to 1.5A of fast-charging power.

The U442-DOCK1 also features a USB-C Power Delivery (PD) port that supports power input up to 20V 3A (60W). It connects to a USB-C wall charger to power the device it's plugged into, as well as peripherals plugged into the USB-A ports.

Highlights

- Mini DisplayPort, VGA and HDMI ports
- Ethernet port supports 10/100/1000 Mbps speeds
- USB-A ports support data transfer rates up to 5 Gbps
- Memory card slots for external memory access
- USB-C Power Delivery port supports power input up to 20V 3A

System Requirements

- MacBook, Chromebook, tablet or laptop with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- DisplayPort*, Mini DisplayPort, VGA, DVI* or HDMI external display
- Ethernet network

Package Includes

- U442-DOCK1 USB 3.1 Gen 1
 USB-C Docking Station
- Owner's manual



Micro SD and SD/MMC memory card slots also provide access to external memory. A 3.5 mm audio jack is convenient for connecting speakers, headphones or a microphone to your connected device.

Features

Convert a Computer into a Versatile Workstation via USB-C or Thunderbolt 3 Port

 Recommended for connecting an external display, accessing Gigabit Ethernet, transferring data and displaying video

Supports USB DisplayPort Alternate Mode

- Connects a Mini DisplayPort, VGA or HDMI external display (one display at a time)
- Supports connection of DVI display via HDMI to DVI adapter (sold separately)
- Supports connection of DisplayPort display via mDP to DisplayPort adapter (sold separately)
- mDP and HDMI ports support video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- VGA port supports video resolutions up to 1920 x 1200, including 1080p, @ 60 Hz

Gigabit Ethernet Port

• Supports true 10/100/1000 Mbps network speeds

3 USB-A Hub Ports

- Support data transfer rates up to 5 Gbps
- Connect USB peripherals, such as a thumb drive or printer, to your device
- Backward compatible with previous USB generations
- BC 1.2-compliant port provides up to 1.5A of fast-charging power to mobile devices

USB-C Power Delivery Port for Charging Portable Devices

- Connects to USB-C wall charger to power the connected computer
- Supports power input up to 20V 3A (60W)
- 15W dedicated to unit and USB-A hub ports
- 45W dedicated to USB-C device the unit is connected to

3.5 mm Mini Stereo Jack

• Supports connection of speakers, headphones or microphone

Micro SD and SD/MMC Card Slots

Memory card slots provide external memory access

Advanced Operation

- Plug-and-play—no software, drivers or external power sources needed
- Automatically resumes operation from hibernation and suspend modes
- Complies with IEEE 802.3az standards
- · Supports full- and half-duplex operations



- Supports IPv4 and IPv6 pack COE to reduce CPU loading
- Supports Wake-on-LAN

Specifications

OVERVIEW		
UPC Code	037332193834	
OUTPUT		
Charging Ports / Amps	1.5A; 3A	
Charging Watts	60	
INPUT		
Bus Powered	Yes	
Product Length (in.)	8.3	
Product Length (cm.)	21.08	
Product Length (ft.)	0.69	
Product Length (m.)	0.21	
BATTERY		
Battery Charging (1.2 Port)	Yes	
PHYSICAL		
Cable Jacket Rating	VW-1	
Color	Silver; White	
Material of Construction	PVC and Aluminum	
Shipping Dimensions (hwd / cm)	2.54 x 13.21 x 16.51	
Shipping Dimensions (hwd / in.)	1.00 x 5.20 x 6.50	
Shipping Weight (kg)	0.23	
Shipping Weight (lbs.)	0.50	
Unit Dimensions (hwd / cm)	1,7 x 7,5 x 13,7	
Unit Dimensions (hwd / in.)	0.67 x 2.95 x 5.39	
Unit Packaging Type	Box	
Unit Weight (kg)	0.10	
Unit Weight (lbs.)	0.22	
ENVIRONMENTAL		



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Operating Temperature Range	32 to 113 F (0 to 45 C)	
Storage Temperature Range	14 to 158 F (-10 to 70 C)	
BTUs	17.1 BTU/Hr	
Power Consumption (Watts)	5	
Operating Humidity Range	10% to 85% RH, Non-Condensing	
Storage Humidity Range	5% to 90% RH, Non-Condensing	
COMMUNICATIONS		
Network Speed	1Gbps	
IEEE Standards Supported	802.3; 802.3u; 802.3az; 802.3x	
CONNECTIONS		
Ports	11	
Dock Connectors	3 x USB3.0, 3.5mm Stereo, RJ45 LAN, HDMI, MINI DISPLAYPORT, VGA, MICRO SD, SD, USB-C CHARGING	
Side A - Connector 1	USB C (MALE)	
Side B - Connector 1	HD15 (FEMALE); HDMI (FEMALE); MINI DISPLAYPORT (FEMALE)	
Side B - Connector 2	(3) USB 3.0 A (FEMALE)	
Side B - Connector 3	MICRO SD (FEMALE); SD (FEMALE)	
Side B - Connector 4	RJ45 (FEMALE)	
Side B - Connector 5	USB Type-C (FEMALE)	
Side B - Connector 6	3.5MM (FEMALE)	
Connector Plating	Nickel	
FEATURES & SPECIFICATIONS		
Max Supported Video Resolution	MDP/HDMI: 3840 X 2160 (4K X 2K) @ 30HZ; VGA: 1920 X 1200 (1080P) @ 60HZ	
Displayport Specification	1.2	
HDMI Specification	1.4	
HDCP Specification	1.4	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Driver Required	No	
Recommended Category Cable	Cat5/Cat5e/Cat6 Cables	
USB Power Delivery (PD) Charging Support	Yes	
Auto MDIX Support	Yes	
Full Duplex Support	Yes	
Suspend Mode Support	Yes	
Remote Wakeup Support	Yes	



Technology	Cat5/5e; Cat6; DisplayPort; HDMI; Stereo Audio; USB; USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); VGA/SVGA; PD Charging	
SD Card Specification	SD; Micro SD	
USB Power Delivery (PD) Charging Specification	2.0	
CERTIFICATIONS		
Certifications	Tested to CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies