



BenQ - Interactive Flat Panel : RE8603

Specifications

ENERGY STAR Unique ID:	2399128
Brand Name:	BenQ
Model Name:	Interactive Flat Panel
Model Number:	RE8603
Product Type:	Signage Display
Panel Type:	TFT-LCD
Screen Size (inches):	85.6
Screen Area (square inches):	3155.77
Native Resolution (pixels):	3840 x 2160
Maximum Luminance (candelas per square meter):	390.0
Total Native Resolution (megapixels):	8.3
Model Features:	Other
Signal or Data Interfaces:	VGA,Other,HDMI,USB
Power Source:	Ac to dc internal power supply
On Mode Power (watts):	137.15
Markets:	United States, Switzerland, Taiwan, Japan, Canada
Sleep Mode Power (watts):	0.29
Tiled Display System:	No
ENERGY STAR Certified:	Yes
ENERGY STAR Most Efficient:	No

Additional Model Information

,RE8603A,; ,RE8603B,; ,RE8603C,; ,RE8603D,; ,RE8603E,

UPC Codes

Captured On:
09/02/2022