

## Offset clamp, with adjustable support screw, complete



### Application:

For clamping workpieces.

### Version:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted



<b>Art. no.</b>	<b>26222 020</b>
<b>For table grooves according to DIN 650</b>	12 mm
<b>Suitable screw DIN 787</b>	M12 x 100 mm
<b>Min./max. clamping range</b>	28-58 mm
<b>Groove width</b>	14 mm
<b>Span iron length</b>	125 mm
<b>Span iron width</b>	40 mm
<b>Thread dimension</b>	M12
<b>Thread length</b>	49 mm
<b>Thickness</b>	20 mm
<b>Distance</b>	44 mm
<b>Length</b>	40 mm

### EAN-Code

402077207 1288