

Workbench undercounter cabinet with 6 drawers

Height 710 mm, width 570 mm, drawers with full extension

Application:

For the individual assembly of a workbench with workbench panel and base.

Execution:

- Solidly welded steel sheet construction
- Drawers with high-quality Delrin rollers
- Drawers with slots all around for inserting compartment rails and dividers
- Drawers with slotted sheet steel bottom for attaching and fixing individual items
- Drawers flush with cabinet housing, no protruding grip handles
- Aluminium grip handles with paper and cellophane strips and lateral cover caps
- Central locking with rotary cylinder security lock, incl. 2 keys
- Suitable insert material for drawers, see no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010

Art. no.	50212 402
Brand	HK
Manufacturer Part Number	50212402
Number of drawers	6 PCS
Pullout type	Full extension
Height	710 mm
Width	570 mm
Depth	680 mm
Drawer width (inner dimension)	450 mm
Drawer depth (inner dimension)	600 mm
With single pull-out safety brake	Yes
Load-carrying capacity per drawer	70 kg
Drawer surface	0.27 m ²
With doors	No
Drawer with slots	Yes
Perforated drawer base	Yes
Central locking	Yes
Lock type	DOM® locking system
Material	Sheet steel
Cabinet colour	Light grey RAL 7035
Colour of front	Gentian blue RAL 5010
Surface	Powder-coated
Gross Weight	71.000 kg
Product Group	5BC



EAN

4039247969241