

Panel trucks with rubberised strip
with 2 support rollers, load-bearing capacity 400 kg

Application:

For transporting panels, sheets and other large parts.

Execution:

- Steel tube construction with steel sheet toe plate
- For longitudinal transportation of large area wood and plastic panels
- Total width 680 mm
- Wheels with plastic rims and roller bearings
- 2 support rollers 50 mm diameter
- Surfaces coated in profile rubber (non-slip) and adjustable hold-down device as tilt protection
- Powder coating: RAL 5007, brilliant blue, durable surface protection, impact and scratch-resistant

Advantage:

- Practical hold-down clamp for tilt protection

Delivery:

Disassembled



Art. no.	50270 362
Brand	FETRA
Manufacturer Part Number	2075
Height	1450 mm
Material of wheel	Solid rubber
Load-carrying capacity	400 kg
Wheel diameter	250 mm
Wheel width	60 mm
Width	680 mm
Toe plate width	200 mm
Toe plate depth	500 mm
Total stop optional	No
Gross Weight	20.000 kg
Product Group	5AB

EAN

4017976020754