

## HIT steel strapping safety cutters

Made in Japan

HIT®

### Application:

For the safe cutting of steel strapping

### Execution:

- Suitable for steel strapping with a max. width of 51 mm and a max. thickness of 1.2 mm
- Lever transmission for easy cutting
- Lower part with narrow shoe for securely threading in even heavily pre-tensioned strapping
- Upper part with safety clamping device that prevents the cut strap from snapping open
- Non-slip rubber handles



<b>Art. no.</b>	<b>53751 650</b>
<b>Brand</b>	HIT
<b>Manufacturer Part Number</b>	480523
<b>Length</b>	600 mm
<b>Material of handle</b>	1-component plastic
<b>Knife insert length</b>	51 mm
<b>Max. material thickness for steel</b>	1.2 mm
<b>Gross Weight</b>	3.000 kg
<b>Product Group</b>	580

### EAN

4953830075068