



Components
metal parts

Bauteile
Metallteile

Materials / Material
brass / Messing

Finish / Oberfläche
nickel plated /
vernickelt

gasket

Dichtung

silicone/Silikon

Environmental
operating temp.
protection class
RoHS compliant

Umgebung
 (b) Betriebstemperatur
 Schutzklasse
 RoHS konform

(a) -50°C / +155°C
 IP 68 (IEC 60529)
 2002/95/EC

And./ rev. index	Änderungs-Nr. / revision code	Datum/ date	Name/ name	gez./ drawn	Datum/ date	Name/ name	Gewicht/ weight [g]
				gepr./ appr	10.01.2013	MA	
					10.01.2013	BJ	ca./approx.
				Maßstab/ scale	Benennung/ title		
				2:1	N/UHF Protective Cap N/UHF-Abdeckkappe		
				Unterl. Maße/ dim. without tolerances according to	Unterl./ doc. type	Zeichnungsnr./ drawing no.	
				K	H00010A1121		 Maße/ dimensions: mm
b	25340	08.11.2013	MA	Ersatz für/ replaces			
a	24528	10.01.2013	MA	Zeichnung vom 21.09.2000			Original : DIN A4
							Blatt/ sheet 1 von/ of 1