

Euromas Aluminium / Euromas F05

Enclosure, aluminium



A 119

Order no.: 01119000

* = Available on request.

Characteristics

Colour of enclosure group

Grey, similar to RAL 7001

Protection class

IP 66

Enclosure Material

G Al Si 12, PU foamed seal

For details see Technical Information

Scope of delivery

Lid and base, lid screws made of V2A, earthing screw

Note

On the A 198, because of the wall-mounting drill holes inside the sealed lip, expert sealing of the wall-mounting is necessary to achieve protection class IP 66.

G = design with transparent lid (PC)

Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a pressure compensation element.

» Additional information


20.02.2020

Dimensions

Dimensions

122 x 120 x 81 mm

Product drawing



Technical documentation / Downloads

Technical drawings

3D product data in STEP format: Registration necessary
Product drawing in PDF format: 01119000 A-119.pdf (78.8 KB)
Product drawing in DXF format: 01119000 A-119.dxf (505.0 KB)
Drawing for mechanical processing: 01119000 A-119-G.dxf (304.2 KB)

Milling contours are shown here as a DXF file. (Sub D, USB, HDMI, cable glands, ...)

Works Test Certificates

682 WPZ-Euomas-Aluminium DE.pdf (163.7 KB)
682 WPZ-Euomas-Aluminium EN.pdf (143.7 KB)

Product information

Euomas Aluminium F05 GB.pdf (1.8 MB)

Matching accessories



Capstan-headed screws, sealable

21007955 KP

For A 119, A 122, A 124-125, A 130, A 135-190, A 196-197



Allen cheese-head screw for lid

21007950 IS

For A 119, A 122, A 124-125, A 130, A 135, A 140-168, A 170-190



Mounting panels, laminated paper (P 305-329) or galvanised sheet steel (P 330-355)

21001600 M

For A 119-120, P 332



Earthing bars with fitted terminal clamps

21004600 E

For A 119-120, P 332



Wall brackets, screw-on at rear

21004300 WL

For A 119-198, P 330-355



DIN rails DIN EN 60715 TH 15, galvanised steel

21003205 TS 15

For A 119-120, P 332



DIN rails DIN EN 60715 G 32, galvanized steel

21003200 TS 32

For A 119-120, P 332



DIN rails DIN EN 60715 TH 35, galvanized steel

21003210 TS 35

For A 119-120, P 332



Set of hinges

21007800 SCHED