


E11552



Wirable socket

SDOGF030MSSFKPG



Application

Special feature Gold-plated contacts

Electrical data

Operating voltage [V] < 45 AC / < 70 DC
Protection class III
Max. current load total [A] 4

Operating conditions

Ambient temperature [°C] -25...90
Protection IP 68

Mechanical data

Weight [g] 17
Materials PA
Material nut brass, nickel-plated

Remarks

Pack quantity 1 pcs.

Electrical connection

insulation displacement technology: 0.14...0.38 mm²; Core insulation: PVC / TPE; (Ø 1.0...1.6 mm); Cable sheath: Ø 3...5 mm


Electrical connection - socket

Connector: 1 x M8, straight; Moulded body: PA; Locking: brass, nickel-plated; Contacts: gold-plated

E11552

Wirable socket

SDOGF030MSSFKPG



Connection

