


FT-30-A-A-M8/3M

Fibre optics



Product characteristics
Diffuse reflection sensor

M8

Range 45 mm

Connection to fibre optic amplifiers type OIF

Range

Range

OIF: 45 mm

Environment

Ambient temperature

[°C]

-40...290

Mechanical data

Design

straight

Length

[mm]

3000

Min. bending radius

[mm]

30, for fixed installation

Fiber arrangement



Fibre optic

glass

Sensing head

aluminium

Sheathing

aluminium; adapter: polyamide

Weight

[kg]

0.232

Accessories

Accessories (included)

2 hexagon nuts; M8; stainless steel; 2 tooth lock washers; 1 knurled nut; M30

Remarks

Pack quantity

[piece]

1