



Part no.: 50113421
TKS 50x50.UV.HT
Reflector



Figure can vary

Contents

- Technical data

Part no.: 50113421 – TKS 50x50.UV.HT – Reflector

Technical data

Special design

Special design	Heat resistant
----------------	----------------

Mechanical data

Design	Rectangular
Mounting dimension, width	
Reflection surface width	47 mm
Mounting dimension, height	
Reflection surface height	48 mm
Mounting dimension, thickness	8.7 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Coating	UV-protection
Type of fastening	Adhesive Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 120 °C
--------------------------------	----------------

Certifications

Degree of protection	IP 40
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467