



FXx*1)S15-K49

e.g. F37S15-K49

*1) xx No. of contacts 09, 15, 25 or 37

xx	A (mm)	B (mm)	C (mm)	D (mm)
09	25	30,8	18,5	10,16
15	33,3	39,1	26,8	17,78
25	47	53	40,7	30,48
37	63,5	69,3	56,9	45,72

3	xx	Signal contact	S15 / Brass	0,2µm Au / IDC AWG28
2	1	Shell	Steel	tin plated, without stamp
1	1	Insulator	PBT (-55°C - +130°C)	black
No.	St.	Part	Type Description / Material	Surface plating / Colour / Class

Measurement without tolerance acc. to ISO 2768-m		SCALE	
NAME / DATE	sschref	2:1	TITLE
DRAWN	07-10-2008		D-Sub-IDC-Ribbon-Connector
CHECKED	10-10-2008		
	Digitrinder		
	10-10-2008		

1	REV.	DATE	CH-NO.	DWG. NO.	REV.
				FxxS15-K49	1
				ORIGINAL DIN A3-DRAWING AS A FILE	PAGES 1
				REPLACEMENT FOR:	FxxS15-K49 g

