

THE NEW

LOW COST WATERPROOF CONNECTOR

These products are versatile cable connectors intended for use with circular profile cables, either indoors or outdoors.

The TEETUBE is rated at IP 68 and, therefore, can be used underwater or underground. It is supplied as a ready to use kit complete with mounting clip.

- Tested to IP 68 at 5 bar
- Can be used underwater and underground
- 3 and 5 pole versions
- Available in a wide range of body colours
Black and Grey (Solid Colours)
Or Red, Green, Orange and Clear (Translucent)
- Safe, convenient and simple to use
- Compact design
- Wide cable range





Actual Size - 3 Pole



Ordering Information

Catalogue No.	Number of Poles	Cable Gland Size	Body Colour	Gland Colour
TTK 20 BK-SD	3	M20	Black	Black
TTK 20 GY-SD	3	M20	Grey	Grey
TTK 25 BK-SD	5	M25	Black	Black
TTK 25 GY-SD	5	M25	Grey	Grey
TTK20 CR-BK	3	M20	Clear	Black
TTK 20 CR-GY	3	M20	Clear	Grey
TTK 25 CR-BK	5	M25	Clear	Black
TTK 25 CR-GY	5	M25	Clear	Grey
TTK 20 RD-BK	3	M20	Red	Black
TTK 20 RD-GY	3	M20	Red	Grey
TTK 25RD-BK	5	M25	Red	Black
TTK 25 RD-GY	5	M25	Red	Grey
TTK 20 GN-BK	3	M20	Green	Black
TTK 20 GN-GY	3	M20	Green	Grey
TTK 25 GN-BK	5	M25	Green	Black
TTK 25 GN-GY	5	M25	Green	Grey
TTK 20 OE-BK	3	M20	Orange	Black
TTK 20 OE-GY	3	M20	Orange	Grey
TTK 25 OE-BK	5	M25	Orange	Black
TTK 25 OE-GY	5	M25	Orange	Grey

Dimensions



A Selection of the colour options available



Snap fit Mounting Clips

Specifications

Number of Poles	Cable Diameter	Wire Size	Voltage Rating	Current Rating	Operating Temperature
3	5 mm (min) 13 mm (max)	3 x 4 mm ²	450V	32A (EN 60998)	-20 to +100°C
5	8 mm (min) 17 mm (max)	5 x 4 mm ²			

Use TEETUBE to connect to your:

