# GCJ32ER71C226KE01# "#" indicates a package specification code.




















< List of part numbers with package codes > GCJ32ER71C226KE01L , GCJ32ER71C226KE01K

### Shape



L size	3.2 ±0.4mm
W size	2.5 ±0.3mm
Tsize	2.5 ±0.3mm
External terminal width e	0.3mm min.
Distance between external terminals g	1.0mm min.
Size code in inch(mm)	1210 (3225M)

#### Notes

Resin external electrode products

### References

Packaging	Specifications	Minimum quantity
L	ф180mm Embossed taping	1000
К	ф330mm Embossed taping	4000

Mass (typ.)	
1 piece	110mg
φ180mm Reel	168g

## **Specifications**

Capacitance	22μF ±10%
Rated voltage	16Vdc
Temperature characteristics (complied standard)	X7R(EIA)
Capacitance change rate	±15.0%
Temperature range of temperature characteristics	-55 to 125°C
Operating temperature range	-55 to 125°C

1 of 1



<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

