






















Precision Slotted Screwdrivers



SKU	Product	Size Slotted	OAL MM	Blade Length Inch
26008	 Precision Slotted .80 (1/32") x 40mm	0.8mm	120	1.6
26010	 Precision Slotted 1.0 (.039") x 40mm	1.0mm	120	1.6
26012	 Precision Slotted 1.2 (3/64") x 40mm	1.2mm	120	1.6
26015	 Precision Slotted 1.5 (1/16") x 40mm	1.5mm	120	1.6
26018	 Precision Slotted 1.8 (.070") x 40mm	1.8mm	120	1.6
26020	 Precision Slotted 2.0 (5/64") x 40mm	2.0mm	120	1.6
26022	 Precision Slotted 2.0 (5/64") x 50mm	2.0mm	145	2
26023	 Precision Slotted 2.0 (5/64") x 100mm	2.0mm	180	3.9
26025	 Precision Slotted 2.5 (3/32") x 50mm	2.5mm	145	2
26027	 Precision Slotted 2.5 (3/32") x 100mm	2.5mm	195	3.9
26028	 Precision Slotted 2.5 (3/32") x 150mm	2.5mm	245	6
26030	 Precision Slotted 3.0 (1/8") x 50mm	3.0mm	145	2
26032	 Precision Slotted 3.0 (1/8") x 60mm	3.0mm	170	2.4
26033	 Precision Slotted 3.0 (1/8") x 100mm	3.0mm	210	3.9
26034	 Precision Slotted 3.0 (1/8") x 150mm	3.0mm	260	5.9
26035	 Precision Slotted 3.5 (9/64") x 60mm	3.5mm	170	2.4
26040	 Precision Slotted 4.0 (5/32") x 60mm	4.0mm	170	2.4
26041	 Precision Slotted 4.0 (5/32") x 100mm	4.0mm	210	3.9
26042	 Precision Slotted 4.0 (5/32") x 150mm	4.0mm	260	5.9