

## Coaxial Cable Connector 21\_BNC-50-3-12/133\_N

### Description

Straight cable jack

Interface standards

IEC 60169-8\_MIL-STD-348A/301\_CECC 22120



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	4 GHz

#### Mechanical Data

Centre contact	soldered
Outer contact	clamped
Weight	0.0147 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Gasket	VMQ (Silicone rubber)	

### Related Documents

Outline drawing	DOU-00007471
Catalogue drawing	DOU-00007473
Assembly instruction	DOC-0000179064

### Ordering Information

Single package	21_BNC-50-3-12/133_NE
----------------	-----------------------

### Additional Information

Suitable cables	RG_58_C/U, RG_223_/U, ENVIROFLEX_142, RG_400_/U, ASNE0293 XF
-----------------	--