

EAO – Your Expert Partner for Human Machine Interfaces

84-8001.5620 - Indicator element

84-8001.5620 - Indicator element




Attention: The preview is based on a sample product. This can differ from your current configuration.

Attribute

Forward voltage	V @
Illumination colour	Green
Kind of illumination	Single-LED
IP Protection	IP40
Lumi. Intensity	mcd
Operating voltage	24 V DC $\pm 10\%$
Terminal	Plug-in terminal
Weight	0.005 kg

Wiring diagrams



Additional information

LED and built-in resistor included

Standard version: Cable length 300 mm with insulated ferrule, plug-in terminal 2.8 mm x 0.8 mm

Other options on request: Customisation of cable and connectors, rear side fully sealed (IP 67)

Protection degree (rear side): IP 40, upgrade to IP 67 with plug Part No. 84-900 possible. With applications where strong vibrations occur, the plugs may become loose

Luminosity and wave length variations caused by LED manufacturing processes may cause slight differences regarding the illumination. The customer has to decide what resistor shall be used to the LED