

Electronic handheld rev meters

For non-contact rotational speed measurement

ORION[®]

Application:

For non-contact rotational speed measurement

Execution:

- Non-contact measurement using a red, modulated light beam and a reflection marker
- 5 digit LCD display
- Error limit: 0.02% of display value (± 1 digit increment)
- Update time: 1 s
- Measuring distance: optical max. 600 mm
- Memory function: last value measured, maximum value, minimum value, mean
- Shutdown: automatically 30 s after last key press, measured value saved
- Housing: Plastic with holster

Delivery:

Case with basic device, reflection markers, 2 x 1.5 V AA batteries, calibration certificate, operating instructions



Art. no.	39350 025
Brand	ORION
Manufacturer Part Number	39350025
Max. measurement distance	600 mm
Error limit (%)	0.02 %
Gross Weight	0.523 kg
Product Group	301

EAN

4039247611560