

## Moisture analyser DLB

**KERN**

### Application:

For fast and efficient working thanks to the graphic display

### Execution:

- Fast and efficient working thanks to the graphic display
- Backlit graphic LCD display, 11 mm digit size
- 6 direct keys for quick access to the main functions
- with intuitive graphic display

### Delivery:

with 10 sample trays, power supply unit and work protection cover



<b>Art. no.</b>	<b>49000 078</b>
<b>Brand</b>	KERN
<b>Manufacturer Part Number</b>	DLB 160-3A
<b>Type description</b>	DLB 160-3A
<b>Reproducibility</b>	0.001 g
<b>Max. weight measuring range</b>	160 g
<b>Digit increment, weight</b>	0.001 g
<b>Linearity</b>	0.003 g
<b>Data transmission type</b>	RS232
<b>Display type</b>	Graphic LCD
<b>Digit height</b>	11 mm
<b>Plate diameter</b>	100 mm
<b>Gross Weight</b>	6.562 kg
<b>Product Group</b>	447

### EAN

4045761133952