

## Pneumatic random orbital sander RRI-T6250-5CV

Grinding wheel diameter 150mm, eccentric stroke 5 mm



### Application:

For two-hand use

### Execution:

- Ergonomic shape
- Noise-dampened air outlet
- Sanding pad with hook-and-loop surface
- Adjustable speed
- Design for central suction (for 32-mm diameter hose)
- Eccentric stroke: 5mm

### Advantage:

- Special vibration damping: Housing with rubber surface for a good grip with the palm of your hand

### Delivery:

Hook-and-loop plate 150 mm with 15 holes



<b>Art. no.</b>	<b>75066 012</b>
<b>Brand</b>	RED ROOSTER
<b>Manufacturer Part Number</b>	RRI-T6250-5CV
<b>Model</b>	RRI-T6250-5CV
<b>Valve design</b>	Lever valve
<b>Washer diameter</b>	150 mm
<b>Oscillating diameter</b>	5 mm
<b>Max. idle speed</b>	12000 rpm
<b>Air consumption</b>	4.9 l/s
<b>Connection thread</b>	1/4 inch
<b>Sound-pressure level</b>	73 dB
<b>Inner hose diameter</b>	6.5 mm
<b>Length</b>	262 mm
<b>Weight</b>	1 kg
<b>Gross Weight</b>	1.300 kg
<b>Product Group</b>	7AE

### EAN

871798120428 1