

Ring bolt

Screwable sling point, 360° rotation

CARTEC

Application:

For the safe attachment of loads.

Execution:

- Forged, high-strength annealed
- 100% Magnaflux crack-tested in accordance with DIN EN 1677-1
- captive hexagon socket screw,
- can be rotated 360°
- designed for up to 20,000 strokes at full load
- Powder-coated surface: salmon-coloured

Advantage:

- 4-fold safety
- Can be set in the direction of force to avoid accidental unscrewing or overscrewing



Art. no.	77232 110
Brand	CARTEC
Manufacturer Part Number	C807XHT10
Design	Without key
Thread dimension	M10
Load-carrying capacity	0.4 t
Distance between lower edge of retainer holder and retainer	33.7 mm
Bracket width	9.8 mm
Bracket height	10 mm
Outer diameter	46 mm
Diameter 2	30 mm
Internal width	25 mm
Width of support plate	25.5 mm
Usable thread length	15 mm
Width across flats	6 mm
Weight	0.12 kg
Gross Weight	0.120 kg
Product Group	775

EAN

80134299 1602 1