

PrimaVision Mini for CDM

HID-PV m 20 /I CDM 220-240V 50/60Hz


Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data

Operating and Electrical		Mechanical and Housing	
Input Voltage	220 to 240 V	Housing	Independent
Line Frequency	50 to 60 Hz		
Input Frequency	50 to 60 Hz	Approval and Application	
Earth Leakage Current (Max)	0.5 mA	Approval Marks	F-Marking CE marking ENEC certificate CB Certificate
Inrush Current Width	0.25 ms		
Inrush Current Peak (Max)	15 A	Product Data	
Number of Products on MCB (16A Type B) (Nom)	24	Order product name	HID-PV m 20 /I CDM 220-240V 50/60Hz
		Full product name	HID-PV m 20 /I CDM 220-240V 50/60Hz
		Full product code	872790089060000
		Order code	913700646266
		Material Nr. (12NC)	913700646266
		Numerator - Quantity Per Pack	1
		EAN/UPC - Product/Case	8711500881632
		Numerator - Packs per outer box	10
		EAN/UPC - Case	8727900890600
Wiring			
Cable Length From Device to Lamp	2 m		
Connector Type	Insert		
Temperature			
Ambient temperature range	-20 °C to 45 °C		
T-Case Lifetime (Nom)	75 °C		
T-Case Maximum (Max)	75 °C		

PrimaVision Mini for CDM

Dimensional drawing



Product	D1	C1	A1	A2	A3	B1
HID-PV m 20 /I CDM 220-240V 50/60Hz	4.8 mm	34.0 mm	234.7 mm	225.1 mm	202.0 mm	49.4 mm

